



- ★ : Require proper type of adhesive.
- ★a : Two-component adhesive (Epoxy resin system)
- ★b : Instant adhesive
- ★c : Thread locking adhesives (Anaerobic adhesive)
- * : Grease (Grease that doesn't affect plastic)

No.	PART No.	DESCRIPTION	Q'TY USED	NOTE
1	JB50-1	JB50 base assembly		
2	JB50-2	Head mount platform cushion rubber	1	
3	JB50-3	φ75mm adapter	1	
4	JB50-4	Ball cup	1	
5	JB50-5	Ball cup lock bolt	1	2 Pcs. set
6	JB50-6	Hex key wrench holder	1	
7	JB50-7	Hex key wrench	1	
8	JB50-8	Boom friction knob	1	
9	JB50-9	Joint shaft knob	1	
10	JB50-10	Telescopic locking knob	3	
11	JB50-11	Telescopic locking lever	1	
12	JB50-12	Telescopic locking screw	2	2 Pcs. set
13	JB50-13	Weight fixing nut	2	
14	JB50-14	Threaded weight shaft	1	
15	JB50-15	Serration	2	
16	JB50-16	Cushion rubber A	2	
17	JB50-17	Pan friction knob	2	
18	JB50-18	Bowl clamp	1	
19	JB50-19	Safty lock assembly	1	
20	JB50-20	Cushion rubber B	2	
21	JB50-21	Cushion rubber C	1	
22	JB50-22	Holding band	1	
23	JB50-23	Fine tuning weight	1	W = 1 kg